




MODEL F1003 CODE PRACTICE SET



"TTC" model F1003 is an excellent training key for all students of code.

1. The wide flat plastic base resists sliding and provides stable foundation for use on any surface.
2. The sturdy key is adjustable for both tension and contact clearance to fit any individual "touch."
3. The buzzer is also adjustable for high, medium or low frequency to suit the individual need.
4. Two binding posts are provided for use with a headset. Two sets can be connected together for talking to each other with the posts connected by wires.
5. Battery : 1.5 volts standard flash light cell (UM-1A).

How to adjust the buzzer

If the buzzer doesn't work, please re-adjust it according to the following instruction. Though the buzzer is factory adjusted, it is apt to be out of tune because of effects of transit.

Instruction.....

Please remove the square metal cover of buzzer, and adjust the supporting bolt (B) to keep 1 m/m interval between the magnet and diaphragm, and fix at the point with the nut.

Secondly, screw the adjustor (A) slowly into, until you get the maximum sound. When you reach the best tone, fix it with the round locking nut.